

GN 8120 USB – Quick Set Up Guide

Xten ineen Softphone

The GN 8120 USB provide in-line control of basic softphone call functions, such as off-hook/on-hook, volume, and mute, and incorporate digital signal processing to enhance audio quality. No external drivers are required for integration with the Xten ineen Softphone basic controls (Plug and Play).

Required Components:

- 1 Laptop or PC
- 2 Available 1.0 or 2.0 USB Port
- 3 Xten ineen version 1.1
- 4 GN 8120 USB
- 5 Any GN Quick Disconnect Headset
 - ▶ GN 2100 – recommended
 - ▶ GN 2200
 - ▶ GN Profile
 - ▶ GN Advantage Plus



Installation:

Step 1 – Set-up the product

- ▶ Connect GN QD Headset to GN 8120 USB and Plug GN 8120 USB into any available USB port.
- ▶ Wait for the device to fully install (Plug and Play).

Step 2 – Download the software

- ▶ Go to: <http://www.ineen.com>.
- ▶ Download and Install ineen Softphone for Windows or Mac OS X.
- ▶ Follow set up instructions.

Note: If ineen does not register, your PC is most likely behind a firewall with enhanced security. Contact your IT department to resolve this issue, or simple install ineen on a PC that has access to an open broadband connection (for example a home broadband connection).

Step 3 – Tune the Product


- ▶ Right mouse click on **ineen** Softphone surface and select **Tuning Wizard**.
- ▶ Tuning Wizard will appear, click **next**. Select **configure only a headset**, click **next**.
- ▶ Select **GN 8120** within the drop down windows for speaker and microphone, click **next**.
- ▶ Adjust the **volume**, click **next**. Adjust **microphone**, click **next**.
- ▶ Select **internet connection speed**, click **next** then **finish**.
- ▶ Restart Softphone and GN 8120 USB will function properly.

Basic Call Function Integration:

The GN 8120 USB contains three call function buttons with associated call function LEDs and a volume rocker for adjusting the audio volume heard on the headset. The mapping between the three function buttons/LEDs and Xten ineen Softphone is generally as follows:

Functions:

- ▶ **Green button** – on-hook/off-hook, answer/hang-up call.
- ▶ **Green button LED** – Indication of on-hook/off-hook, incoming call.
- ▶ **White button** – Not currently in use – Future.
- ▶ **White button LED** –Not currently in use – Future.
- ▶ **Red button** – mute on/off.
- ▶ **Multi-Color LED** –Indication of mute on/off.



Sound Quality) Comfort) Durability



www.gnnetcom.com

Free Manuals Download Website

<http://myh66.com>

<http://usermanuals.us>

<http://www.somanuals.com>

<http://www.4manuals.cc>

<http://www.manual-lib.com>

<http://www.404manual.com>

<http://www.luxmanual.com>

<http://aubethermostatmanual.com>

Golf course search by state

<http://golfingnear.com>

Email search by domain

<http://emailbydomain.com>

Auto manuals search

<http://auto.somanuals.com>

TV manuals search

<http://tv.somanuals.com>