# 5500B

## PMD ANALYZER III

FTB-5500B





Patented design\*: test through EDFAs





<sup>\*</sup> Pantent pending, International PCT Publ. No.WO2004/070341. Measurement method approved by TIA-FOTP-124A

## Measuring PMD the Fast Way

PMD represents a significant danger to both legacy and newly deployed networks. And as systems of 10 Gb/s and faster develop, PMD concern and awareness continue to grow. EXFO's FTB-5500B PMD Analyzer helps you get ahead in the field. Whether you need to verify the capacity of legacy fiber or maintain a network, the modular FTB-5500B is fast, reliable, and ready to go.



### Less than 5-Second Testing Time

The rugged FTB-5500B features a market-leading PMD measurement time of less than five seconds—for any PMD value. Improve your testing efficiency. Reduce testing costs. Test more fiber, and test it faster.

# A Unique Approach to Testing Through EDFAs and Removing Auto-correlation Peaks

The FTB-5500B's unique technology allows for both the auto-correlation and cross-correlation to be known. Therefore, any spectral shape of source can be used. The auto-correlation peak is thus removed, and higher accuracy and resolution are obtained. PMD of 0 ps can be measured. In addition, a signal transmitted through EDFAs can be analyzed for total link PMD. Calibration is traceable to NIST.

# 15 - 25 - 10 - 25 - 10 - 20 - 10 0 0 10 20 30

#### **KEY FEATURES**

- No auto-correlation peak, for increased accuracy and resolution
- Testing through EDFAs (above 120 EDFAs)
- Under five-second testing time for any range
- Minimum measurable PMD: 0 ps

### Field-Proof, Advanced Technology

#### The FTB-400 UTS Advantage

Housed in the tough, light-magnesium-shell and rubber-bumpered FTB-400 Universal Test System, the FTB-5500B PMD Analyzer will survive knocks, bumps and drops. Combine up to seven single-slot, field-interchangeable modules in the powerful FTB-400 for simultaneous support of multiple testing applications (CD analyzer, OTDR and OLTS, among others).

#### The FLS-5800 CD/PMD Analyzer Source Advantage

A single light source, the FLS-5800 CD/PMD Analyzer Source, can help you characterize both chromatic dispersion (CD) and polarization mode dispersion (PMD)-reducing testing time and minimizing the potential for human error.

#### Second-Order PMD

Particularly important in multichannel transmission, second-order PMD is derived from the measured PMD value. EXFO's software provides second-order PMD delay and coefficient values for telecom fibers. These values allow you to characterize fibers and cables more precisely than simple PMD and better control the transmission quality of high-speed systems.

#### ToolBox Software Solutions

#### PMD Touch and Go

EXFO's ToolBox software suite runs the FTB-400's test module applications. The user-friendly touchscreen provides easy access to menus and functions, for highly productive, yet simple testing in the field.

#### Simple Step-by-Step Measurements

Step-by-step instructions make testing easy and virtually error-free. Both new users and experts can obtain fast, accurate and efficient PMD measurements with minimal training. The analysis software calculates and displays a fiber's total PMD and coefficient, as well as the second-order PMD value and coefficient.

#### **Multiple Measurement Possibilities**

Check for long-term stability. Make several PMD measurements over long time periods with the Multiple Measurement mode, and monitor PMD changes over an extended time.

#### Statistical Result Tables

View your results quickly and easily. After completing multiple tests, the FTB-5500B PMD Analyzer automatically compiles the results in a table and provides statistical analysis:


- Mean PMD delay and coefficient
- Standard deviation PMD delay and coefficient
- Minimum and maximum PMD delay and coefficient


Benefit from powerful statistical analysis for

- Averaging multiple tests on one fiber
- Averaging sets of pre-averaged fibers to produce cable stats
- Gathering data from end-to-end fibers and calculating of total PMD (link creation)

#### **Data Management Features**

Manage all your data with ease. EXFO's software includes various data management features, such as automatic file naming and statistical and table management, as well as custom report generation and batch printing. The software also comes with a file converter, which transforms PMD files into text files.





#### **SPECIFICATIONS**

Wavelength range (nm)		1260 to 1675 (O to U band)	1260 to 1675 (O to U band)		
Measurement range (ps)		0 to 115			
Sensitivity (dBm)		-45¹			
Measuring time (s)		4.5 (for any PMD value)			
Absolute uncertainty (accuracy) <sup>2</sup> (ps)		$\pm$ (0.020 + 2 % of PMD)	± (0.020 + 2 % of PMD)		
Allows measurement through EDFA		Yes (above 120 EDFAs)	Yes (above 120 EDFAs)		
GENERAL SPECIFICATIONS	e				
GENERAL SPECIFICATIONS	3				
Temperature	operating	0 °C to 40 °C	(32 °F to 104 °F)		
		0 °C to 40 °C -40 °C to 70 °C	(32 °F to 104 °F) (–40 °F to 158 °F)		
	operating		,		
Temperature	operating storage	-40 °C to 70 °C	,		

#### Note:

- 1. Typical, for C-band. May be increased with averaging. With the FLS-5800, the typical dynamic range is 47 dB.
- 2. For C-band, assuming averaging over all states of polarization.

#### ORDERING INFORMATION

#### **PMD** Analyzer CD/PMD Analyzer Source

#### FTB-5500B-XX FLS-58XX-XX

Connector \* EI-EUI-28 = UPC/DIN 47256 EI-EUI-76 = UPC/HMS-10/AG

EI-EUI-89 = UPC/FC narrow key EI-EUI-90 = UPC/ST EI-EUI-91 = UPC/SC EI-EUI-95 = UPC/E-2000

EA-EUI-28 = APC/DIN 47256EA-EUI-89 = APC/FC narrow key EA-EUI-91 = APC/SC

EA-EUI-95 = APC/E-2000Example: FTB-5500B-EI-EUI-89

Model FLS-5803 = 1550 nm SuperLED

FLS-5804 = 1625 nm SuperLED FLS-5834 = 1550 nm and 1625 nm SuperLEDs

Connector \*

EI-EUI-28 = UPC/DIN 47256 EI-EUI-76 = UPC/HMS-10/AG EI-EUI-89 = UPC/FC narrow key

EI-EUI-90 = UPC/ST EI-EUI-91 = UPC/SC EA-EUI-91 = APC/SCEA-EUI-95 = APC/E-2000

EA-EUI-28 = APC/DIN 47256

EA-EUI-89 = APC/FC narrow key

EI-EUI-95 = UPC/E-2000

Example: FLS-5803-EI-EUI-89

#### **Polarized Light Source**

FLS-110-XXP-XX Model FLS-110-02P = 1310 nm LEDFLS-110-03P = 1550 nm LEDConnector \*-

58 = FC/APC narrow key 89 = FC/UPC narrow key 91 = SC/UPC

EI-EUI-28 = UPC/DIN 47256 EI-EUI-76 = UPC/HMS-10/A EI-EUI-89 = UPC/FC narrow key EI-EUI-90 = UPC/ST

EI-EUI-91 = UPC/SC EI-EUI-95 = UPC/E-2000EA-EUI-28 = APC/DIN 47256 EA-EUI-89 = APC/FC narrow key EA-EUI-91 = APC/SCEA-EUI-95 = APC/E-2000

Example: FLS-110-02P-EI-EUI-89

\* EXFO Universal Interface is protected by US patent 6,612,750.

#### **Standard Accessories** Safety

21 CFR 1040.10 Class I Laser Product IEC 60825-1: 2001 Class 1 Laser Product User Guide, Certificate of Calibration, connector cleaners.

Find out more about EXFO's extensive line of high-performance portable instruments by visiting our website at www.exfo.com.



#### Rugged Handheld Solutions

- OLTS
- Power meter -Light source
- Talk set



#### Optical Fiber DWDM Test Systems

- OTDR OSA
- -OLTS ORL meter
- -Switch

- -PMD analyzer
- Chromatic dispersion analyzer
- Multiwavelength meter

## Transport/Datacom

- 10/100 and Gigabit Ethernet
- -SONET/SDH (DS0 to OC-192c)
- -SDH/PDH (64 kb/s to STM-64c)
- \_SAN

Tall-fron: 1 900 662 2026 (LISA and Canada) | www.

Corporate Headquarters > 400 Godin Avenue, Vanier (Quebec) G1M 2K2 CANADA | Tel.: 1 418 683-0211 | Fax: 1 418 683-2170 | info@exfo.com

		ion-free. 1 600 663.3936 (USA and Canada)   www.exio.com		
EXFO America	4275 Kellway Circle, Suite 122	Addison, TX 75001 USA	Tel.: 1 800 663-3936	Fax: 1 972 836-0164
EXFO Europe	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85	Fax: +33.1.40.83.04.42
EXFO Asia-Pacific	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241	Fax: +65 6333 8242
EXFO China	Beijing New Century Hotel Office Tower, Room 1754-1755	Beijing 100044 P. R. CHINA	Tel.: +86 (10) 6849 2738	Fax: +86 (10) 6849 2662
	No. 6 Southern Capital Gym Road			

EXFO is certified ISO 9001 and attests to the quality of these products. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor. For the most recent version of this spec sheet, please go to the EXFO website at http://www.exfo.com/specs

In case of discrepancy, the Web version takes precedence over any printed literature.

Printed in Canada 05/06



Free Manuals Download Website

http://myh66.com

http://usermanuals.us

http://www.somanuals.com

http://www.4manuals.cc

http://www.manual-lib.com

http://www.404manual.com

http://www.luxmanual.com

http://aubethermostatmanual.com

Golf course search by state

http://golfingnear.com

Email search by domain

http://emailbydomain.com

Auto manuals search

http://auto.somanuals.com

TV manuals search

http://tv.somanuals.com